

SKINMATIC® KB-M

SKINMATIC® KB-M, metric mounting tool for simultaneous core drilling and cutting of metric threads, especially for thin components



Användningsområden

For simultaneous core drilling and cutting of metric threads. Especially suitable for thin components and sheet metals

Tekniska data

Klassificering ETIM 5:

ETIM 5.0 Class-ID: EC000945

ETIM 5.0 Class-Description: Borr

Klassificering ETIM 6:

ETIM 6.0 Class-ID: EC000945

ETIM 6.0 Class-beskrivning: Borr

Material:

HSSE

Observera

RoHS-direktivet gäller inte.

Fotografierna och ritningar/grafik är inte i skala och motsvarar inte detaljerade bilder av respektive produkt.

Priser som visas i artikeltabeller innan du loggar in är bruttopriser. Exklusive koppartillägg för kabel. Ditt nettopris visas först efter inloggning i Kassan.

Detaljerad information om det totala priset inkl. fraktkostnad samt eventuella tillägg och avgifter visas först i Kassan i steget Prisinformation.

SKINMATIC® KB-M

Art nr	Benämning/storlek	Borrlängd (mm)	Overall length C (mm)	Antal / förp.
SKINMATIC® KB-M				
61791274	M 12 x 1,5	30	130.0	1
61791275	M 16 x 1,5	35	150.0	1
61791276	M 20 x 1,5	40	165.0	1
61791277	M 25 x 1,5	45	185.0	1

Senaste uppdatering (18.02.2020)

©2020 Lapp Group - all rights reserved.

Produktsvar <http://se.lappgroup.com>

Du kan hitta den aktuella tekniska data i motsvarande datablad.

PN 0456 / 02_03.16