

EPIC® SENSOR M12B Screw termination

M12 kontakter

A professional for the PROFIBUS® network: the M12B data connector made of plastic can be assembled with fieldbus cables on site without any special tools whatsoever thanks to the screw connection. It is available in different variants.



Kompletterande automationskomponenter från Lapp



Maskin- och anläggningkonstruktion



Monteringstid



Vattentät

Fördelar

High stability thanks to impact-resistant polyamide.

The service-friendly screw connection makes assembly possible without a special tool, and is suitable for connections which need to be detached again.

When connected, protection class IP 67 can be achieved.

Available in different designs.

Användningsområden

For fieldbus communication in PROFIBUS®-based networks.

Good oil and chemical resistance.

Tekniska data

Klassificering ETIM 5:

ETIM 5.0 Class-ID: EC002062

ETIM 5.0 Class-Description: Sensor-/ställningsstickkontakt

Klassificering ETIM 6:

ETIM 6.0 Class-ID: EC002062

ETIM 6.0 Class-beskrivning: Sensor-aktor-stickkontakt

Material:

PA Polyamid

Skyddsklass:

IP 67

Omgivningstemperatur (drift):

-25 °C till +85 °C

Kontaktmaterial:

Kopparlegering

Senaste uppdatering (11.09.2024)

©2024 Lapp Group - all rights reserved.

Produktansvar <http://se.lappgroup.com>

Du kan hitta den aktuella tekniska data i motsvarande datablad.

PN 0456 / 02_03.16

EPIC® SENSOR M12B Screw termination

Kontaktplätering:

Au (guld)

Observera

Fotografierna och ritningar/grafik är inte i skala och motsvarar inte detaljerade bilder av respektive produkt.

Priser som visas i artikeltabeller innan du loggar in är bruttopriser, exklusive koppartillägg för kabel. Ditt nettopris visas i kassan efter inloggning. Detaljerad information om det totala priset inklusive fraktkostnad samt eventuella tillägg och avgifter visas i kassan under Prisinformation.

EPIC® SENSOR M12B Screw termination

Art nr	PL_POLZAHL	Anslutningstyp	PL_DYN_LEITERQUERSCHNITTFLEXIBEL_MM	PL_DYN_DURCHMESSER_EPIC
381166330	5	Hona	1.5	4.0 - 8.0
381166342	5	vinklad	1.5	4.0 - 8.0
381166336	5	vinklad	1.5	4.0 - 8.0
381166323	5	Hane	1.5	4.0 - 8.0

Senaste uppdatering (11.09.2024)

©2024 Lapp Group - all rights reserved.

Produktansvar <http://se.lappgroup.com>

Du kan hitta den aktuella tekniska data i motsvarande datablad.

PN 0456 / 02_03_16

EPIC® SENSOR M12B Screw termination

