

FLEXIMARK® THERMO WRAP

Temperature indicator for monitoring power cables, with memory effect, available for different activation temperatures (+70 °C or +90 °C).



Maskin- och anläggningkonstruktion



Monteringstid

Fördelar

The attached temperature indicators make visual inspection of electrical equipment possible. A colour change occurs if the temperature is exceeded.

Quickly identifying overheated electrical components makes rapid cause analysis possible. This allows appropriate countermeasures to be initiated to avoid plant downtimes.

24/7 monitoring and the memory effect make it possible to continuously record temperature exceedance, and can act as an early warning of overheating.

Safe, fast and uncomplicated installation.

Suitable for cable outer diameters of up to 33 mm.

Användningsområden

For indicating that temperatures have been exceeded.

Irreversible colour change at temperatures from +70 °C or +90 °C (depending on article).

For use with power cables.

Can be used in dry interiors.

Övrigt

Limitations: These labels are designed to use on electrical equipment and as such electrical safety must be assessed by a competent electrician prior to their application. FLEXIMARK® THERMO WRAP is not suitable for unprotected use outdoors or in direct sunlight. The wraps are vulnerable to degradation and non-performance from prolonged exposure to ultra-violet (UV) light. FLEXIMARK® THERMO WRAP will not prevent electrical faults or fires but will aid in monitoring abnormal temperatures and will give visual indication of abnormal wire insulation temperature above 70 °C/90 °C for whatever underlying cause.

Tekniska data

Klassificering ETIM 5:	EC003592
Färg:	Gul
Material:	Polyester Täckfilm: Polyester Lim: Akryl Material för färgförändring: Giftfritt vitt värmereagerande ämne på en svart absorberande baksida fäst med akryllim.
Temperaturområde:	- Aktiveringstemperatur: +70 °C och +90 °C - Tolerans: +/- 1 °C - Svarstid: 5-20 sekunder - Förvaras i normal rumstemperatur och luftfuktighet

Observera

Fotografierna och ritningar/grafik är inte i skala och motsvarar inte detaljerade bilder av respektive produkt.

Priser som visas i artikeltabeller innan du loggar in är bruttopriser, exklusive koppartillägg för kabel. Ditt nettopris visas i kassan efter inloggning. Detaljerad information om det totala priset inklusive fraktkostnad samt eventuella tillägg och avgifter visas i kassan under Prisinformation.

Senaste uppdatering (23.04.2024)

©2024 Lapp Group - all rights reserved.

Produktansvar <http://se.lappgroup.com>

Du kan hitta den aktuella tekniska data i motsvarande datablad.

PN 0456 / 02_03.16

FLEXIMARK® THERMO WRAP

FLEXIMARK® produkter säljs i förpackningsenhet. T.ex. om du beställer 640 etiketter av LCK 32, behöver du endast beställa 1PU istället för 640 enskilda etiketter

FLEXIMARK® THERMO WRAP

Art nr	E-nummer	Benämning	Storlek (mm)	Förp.
83881120	4222590	FLEXIMARK® THERMO WRAP 70°C -1000	118x15	1000
83881121	4222591	FLEXIMARK® THERMO WRAP 70°C -200	118x15	200
83881122	4222592	FLEXIMARK® THERMO WRAP 70°C -50	118x15	50
83881123	4222593	FLEXIMARK® THERMO WRAP 70°C -20	118x15	20
83881124	4222594	FLEXIMARK® THERMO WRAP 90°C -1000	118x15	1000
83881125	4222595	FLEXIMARK® THERMO WRAP 90°C -200	118x15	200
83881126	4222596	FLEXIMARK® THERMO WRAP 90°C -50	118x15	50
83881127	4222597	FLEXIMARK® THERMO WRAP 90°C -20	118x15	20

Senaste uppdatering (23.04.2024)

©2024 Lapp Group - all rights reserved.

Produktansvar <http://se.lappgroup.com>Du kan hitta den aktuella tekniska data i motsvarande datablad.
PN 0456 / 02_03_16