
ROBOTRAX® System

Cable carrier for 3D movements



Trademarks are legally protected for the TSUBAKI KABELSCHLEPP GmbH as a national or international registration in the following countries: tsubaki-kabelschlepp.com/Trademarks Subject to change

ROBOTRAX[®] System | Overview



Inner widths 27 64 tsubaki-kabelschlepp.com/ robotrax

svstem

Inner

10 31

- 1 Steel cable for transferring extremely high tensile forces
- 2 Tension piece for locking the chain links
- 3 Special plastic for long service life
- 4 Open design
 - Fast cable laying as the cables are simply pressed in
 - Easy checking of all cables
- 5 Protective covers or heat shields made from different materials are available for different environmental conditions
- 6 Quick-release bracket for fixing and continuation
- 7 Strain relief with LineFix clamps
- 8 Protection against hard impacts, excessive abrasion and premature wear as well as limitation of the bending radius through protector

Features

- Suitable for three-dimensional swivel and rotation movements
- Ideal for a long service life of the cables:
 - The bending radius does not fall below the minimum
 - The cables can be separated in three chambers
- Also ideal for turntables







Active return mechanism with the PBU pull back unit



Fast cable laying by simply pressing in the cables



Strain relief for secure fixing of the cables


ROBOTRAX[®] system

ROBOTRAX® System Overview

ы С	Type	ant							Additio-		Page
ŝ	Ţ	Opening variant	h i [mm]	B _i [mm]	Da [mm]	t [mm]	KR [mm]	Radial link rotation [°]	nal load ≤ [kg/m]	d_{max} [mm]	Ра
eviation: e 12	R040	Oper	۲	6	Ø	$\stackrel{\longleftrightarrow}{\rightrightarrows}$	×		Ğ	$\boxed{\oslash}$	
Key for abbreviations on page 12		9	10	27	40	21.5	80	± 450	0,7	8,5	526
	R056	9	14	39	56	32	115	± 300	1,1	11	526
Design guidelines from page 38	R075	9	22	52	75	40	145	± 215	4	18	526
Desi	R085	9	24	54	85	40	175	± 215	5	20	526
al support: Ibelschlepp.de		9	31	64	100	40	195	± 215	6	27	526







ROBOTRAX[®] System | Design principle

ROBOTRAX®

→ Pit	cn
21.	.5 – 40 mm








Chain links

The basic structure of ROBOTRAX[®] consists of plastic links. These have spherical snap-on connections on both sides. This allows the individual links to be snapped together to form a cable carrier.

Protectors ensure that the bending radius does not fall below the minimum in any direction. The links can be rotated in the radial direction (see table values). The cables can be separated in three chambers.





Dimensions and order

Туре	t [mm]	KR [mm]	Radial rotation possible on 1 m length [°]	d [mm]	Number of links per m
R040	21.5	80	± 450	2-8.5	47
R056	32	115	± 300	2 – 11	32
R075	40	145	± 215	3–18	25
R085	40	175	± 215	3 – 20	25
R100	40	195	± 215	3 – 27	25

Order example

\sim	R040].	010].[80] - [1000	
\mathbf{S}	Туре	_	Design*		KR [mm]	_	L _k [mm]	

Calculating the cable carrier length

Cable carrier length L_k $L_k = n \times t$

ROBOTRAX[®] System | Design principle

Steel cable, clamping and tension piece

Fast movements of the robot arms generate high accelerations and therefore high tensile forces on the cable carrier.

To transfer these tensile forces, ROBOTRAX[®] has a hole at the center of each chain link through which the steel cable is pulled. This steel cable takes on the function of force transmission.

The steel cable is fixed with a clamping piece on both sides. ROBOTRAX[®] permits accelerations up to 10 g.

The clamping piece can be used to easily set the chain links to the desired tension and adjust them at any time.

Long service life of the cables and hoses:

The forces are primarily transmitted by the cable carrier and not by cables and hoses.



Dimensions

	R040	R056	R075	R085	R100
Ø cable [mm]	1.8	2.5	3.5	3.5	4.5





Inner widths 27 64

subaki-kabelschlepp.com/ robotrax

Quick-release brackets

The ROBOTRAX[®] is fixed and continued with quickrelease brackets which are attached with two screws.

The quick-release brackets fit on any chain link of the respective size. This means the fixing points can be individually adjusted to the motion sequence.

Quick opening:

Simply unlock, pull out and open the quick-release bracket.


Dimensions and order


	R040	R056	R075	R085	R100
h 1 [mm]	54	70	89	105	120
l ₁ [mm]	15	22	28	30	32
b 1 [mm]	82	86	110	133	150
b ₂ [mm]	50	63	82	96	112
b 3 [mm]	36	48	64	72	70
b 4 [mm]	18	24	32	36	35

Threaded joint on the quick-release bracket:

R040, R056	with hexagon socket screws M4
R075	with hexagon socket screws M6
R085, R100	with hexagon socket screws M8







Please state the desired quantity when ordering.

ROBOTRAX system

Key for abbreviations

on page 12

ROBOTRAX[®] System | System components

Heat shield/protective cover

Heat shield: The heat shield made from aluminumcoated textile fibers protects the ROBOTRAX[®] system and inserted cables against flying sparks, weld spatter and radiated heat.

Protective cover: The protective cover made from coated polyester protects against aggressive cutting fluids, hydraulic oils, fine dust and paint spatter.



Please state when ordering.

Strain relief for cable ties


Design guidelines from page 38

For secure fixing of the cables. The strain relief can be used on either end.

(available for all types)



Technical support: technik@kabelschlepp.de Please state when ordering.



Strain relief LFR

(for types R075, R085 and R100) Secure cable fixing, gentle on the cables.

Multi-layer cable fixing is also possible with double and triple LineFix® clamps. Several systems can be installed in sequence.

LineFix[®] strain reliefs - see page 708.



Please state when ordering.



Conline-engineer.de

ROBOTRAX® System | System components

PBU pull back unit/guide bracket

(available for all types)

PBU: With fast movement sequences and large work envelopes, the relatively long carriers knock against the robot arm. The repeated impact significantly reduces the service life of the cable carrier and the cables within, and the entire system can fail. Downtimes cause high costs and problems in the manufacturing process – so they have to be avoided.



The PBU is available with a variety of different parameters. Please contact us.

Guide bracket: The guide bracket ensures a defined return into the PBU, with the ROBOTRAX[®] gliding through the bracket. This reliably prevents the cable carrier from knocking against the robot arm. Installation of the guide bracket is easy and quick. The bracket is easy to open and allows easy and fast cable laying. The guide bracket can be combined with the standard bracket and is available for all ROBOTRAX[®] sizes.



The service life of the cable carriers and cables is significantly reduced by impact during fast movement sequences and in large work envelopes. The Protector protects the cable carrier against hard impacts, excessive abrasion and premature wear, while also acting as a limitation for the smallest bending radius. Downtimes are minimized. Not the entire cable carrier has to be replaced, but only the Protector in some cases.



Please state when ordering.



ROBOTRA system





tsubaki-kabelschlepp.com/ robotrax

529

ROBOTRAX[®] System | System components


Turntable for quick-release bracket

One additional degree of freedom on the attachments points. When mounted on a turntable, the quick-release bracket can rotate as well, to offer increased flexibility during complex robot movements.



Dimensions

	R040	R056	R075	R085	R100
A [mm]	57	65	82	96	112
B [mm]	57	57	57	70	70
C [mm]	43	43	43	75	75
D [mm]	43	43	43	45	45
E [mm]	36	48	64	72	70
H [mm]	25	25	25	34	34
d₁ [mm]	M6	M6	M6	M6	M6
d₂ [mm]	M4	M4	M6	M8	M8





Set consisting of



Please state when ordering.

Coil spring for quick-release bracket


If the quick-release bracket is mounted on a coil spring, it can move elastically in all directions, deflect in 3 dimensions and spring back.



Dimensions

	R040	R056	R075	R085	R100
A [mm]	52	64	82	96	112
B [mm]	36	48	64	72	70
C [mm]	5	5	6.5	8.5	8.5
L [mm]	110	110	-	-	-
	150	150	-	-	-
	-	-	165	165	165
	-	190	-	-	-
	_	-	230	230	230
	-	-	315	315	315
	-	-	465	465	465

Please state when ordering.



Technical support: technik@kabelschlepp.de

Design guidelines from page 38

ROBOTRAX system

